



Extra Secure Spin Lockout with 1.5 m Cable and Tool

Key Characteristics	Article Number	152268	
	Order Reference	152268	
	Total Qty per Pack	1 Kit / Kit	
	Application(s)	Lockout tagout	
	Quantity	1	
	Brand	Brady®	
	Country of Origin	CN	
	Dimensions	Size - Depth (mm)	40.39 mm
		Size - Diameter (mm)	55.12 mm
Weight (kg)		0.125 kg	
Cable Length (m)		1.50 m	
Cable Diameter		3.05 mm	
Max. Shackle Diameter (mm)		8.13 mm	
Dimensions		55,12 mm (Dia) x 40,39 mm (D)	

Material Characteristics	Brady Material Type	Glass-filled Nylon
	Colour	Yellow
	Cable Material	PVC Coated Steel
Product Features	<u>Max number of padlocks attached</u>	6
	# of Holes	6
	<u>Risk</u>	Mechanical Risk

What's Included	Includes	(1) Cable, (1) Extra Secure Spin Lockout, Yellow (122245), (1) Tool
Compliance	<u>UNSPSC</u>	39121905
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863
	REACH SVHC Status	Part does not contain an SVHC
	REACH Candidate List Date	17 January 2022
	Approval/Compliance	OSHA 1910.147