



3 JAHRE GARANTIE YEARS WARRANTY

ANSMANN HS5R

- Professional mobile spotlight made from robust ABS plastic - extremely bright thanks to the latest 5W LED technology from CREE
- Permanently installed li-ion rechargeable battery (3.7V / 2600mAh)
- Three lighting functions can be selected via the function button: 100% lighting power / 25% lighting power / flashing light
- Huge lighting range: Up to 500m at 100% lighting power, up to 255m at 25% lighting power
- Extremely bright and concentrated light: 420 lumens at 100% lighting power with 2h battery life,
- 105 lumens at 25% lighting power with 9.5h battery life. 16h battery life in flashing mode.
- The extra powerful mounting magnet fastens the lamp to any metallic object
- Can also be used as an emergency light by activating the mains failure function
- Includes charge cradle with wall bracket for simple mounting
- Includes orange filter disc for use as a warning light
- Protection class IP20

INFORMATION

Product name	HS5R
Part No.	1600-0222
EAN-Code	4013674139828
Customs tariff number	85131000000
Material Group	02
Product content	Lamp, charge station, wall plugs and screws, USB cable, coloured filter disc, operating instructions

Product	215,5 × 81,5 × 105 mm / 0 g
Packing + Product	136 × 100 × 250 mm / 963 g
Packing Unit	6 (428 × 220 × 280 mm)

