



3 JAHRE
 YEARS
 GARANTIE
 WARRANTY

ANSMANN HD250RS

- High-quality, multifunctional head lamp made from robust ABS plastic
- Cree LED for long distance and COB LED for close range, guaranteeing the right light for a multitude of applications
- The HD250RS combines the best optics and the latest technologies – enabling the lamp to be switched on and off through hand gestures when in sensor mode
- The lamp head can be individually adjusted with an incline angle up to 45°
- Super-light with flexible, adjustable head band, and so comfortable to wear (just 52g incl. batteries)
- IP54 protection rating (protected from dust and splashed water)
- Powerful: Max. 250 Lumens provides a light range of up to 51 metres!
- Integrated rechargeable battery pack with 3.7V and 1200mAh (4.44Wh) takes care of the energy required

INFORMATION

Product name	HD250RS
Part No.	1600-0224
EAN-Code	4013674139873
Customs tariff number	85131000000
Product content	HD250RS, micro-USB cable, operating instructions

Product	58 × 36,5 × 43,5 mm / 80 g
Packing + Product	125 × 50 × 272 mm / 149 g
Packing Unit	6 (215 × 135 × 295 mm)

