



GARANTIE WARRANTY
JAHRE YEARS
10

ANSMANN WFL2400S

- ANSMANN Luminary Sense floodlight for wall mounting with 30 W SMD LEDs and a lighting power of up to 2.400 Lumen
- Integrated movement detector with a detection range of up to 12m and a detection angle of 180° horizontally and 90° vertically
- Adjustable lighting intensity - the lighting characteristics at which the floodlight should activate can be adjusted at any time
- The lighting time can be set from ca. 10 seconds to up to 10 minutes!
- Very flat construction - housing made from robust aluminium and ABS – extremely shock-resistant
- Protection rating IP54 ensures dust and water protection, enabling use indoors and out
- Full power straight away thanks to the latest SMD LED technology
- Very pleasant LED light with a colour temperature of 5000K (daylight)
- The angle of the spotlight can be adjusted vertically though 190° thus enabling the light to be placed at the desired location
- Integrated H05RN-F cable with a length of 20 cm for firm and flexible connection with low mechanical stresses in dry, damp and wet rooms

INFORMATION

Product name	WFL2400S	**Product**	235 × 35 × 200 mm / 1197 g
Part No.	1600-0285	**Packing + Product**	246 × 50 × 265 mm / 1476 g
EAN-Code	4013674154494	**Packing Unit**	6 (330 × 262 × 285 mm)
Customs tariff number	85131000000		
Product content	WFL2400S, operating instructions		


4 013674 154494