



3 JAHRE GARANTIE
 YEARS WARRANTY

ANSMANN WL450R slim

- Professional work lamp with robust plastic housing
- 2 switch functions – Main LED (6W COB) / Auxiliary LED (3W)
- Power supply: Integrated Li-ion 3.7 V rechargeable battery with safety electronics
- Max. 450 lumens
- Up to 30 hours of lighting with the auxiliary LED / up to 4.75 hours with the main LED
- Protection class IPX3
- Can be charged via the Micro USB cable (included)

INFORMATION

Product name	WL450R slim
Part No.	1600-0304
EAN-Code	4013674156450
Customs tariff number	85131000000
Product content	WL450R slim, micro-USB cable, operating instructions

Product	306 × 40 × 25 mm / 175 g
Packing + Product	125 × 31 × 422 mm / 273 g
Packing Unit	32 (805 × 270 × 320 mm)

