



**3** JAHRE  
 GARANTIE  
 YEARS  
 WARRANTY

### ANSMANN WL230B

- Workshop lamp with the latest COB LED technology & small auxiliary light on the lamp head
- Robust plastic housing, particularly resistant to mechanical stresses
- Swivelling lamp body, locking base with integrated magnets and clip function
- Fold-out, hook that can be swivelled through 360°
- Lighting power 230 lumens (main light) / 100 lumens (auxiliary light)
- Battery life up to 4 hours / ca. 7 hours
- Incl. 3× ANSMANN AAA alkaline batteries

### INFORMATION

<b>Product name</b>	WL230B
<b>Part No.</b>	1600-0355
<b>EAN-Code</b>	4013674166442
<b>Customs tariff number</b>	8513100000
<b>Product content</b>	WL230B, 3× AAA batteries, operating instructions

<b>Product</b>	222 × 46,3 × 35,3 mm / 172 g
<b>Packing + Product</b>	268 × 52,5 × 40,5 mm / 203 g
<b>Packing Unit</b>	9 (240 × 205 × 295 mm)

