



3
 JAHRE
 YEARS
 GARANTIE
 WARRANTY

ANSMANN HS4500R-DUO

- Professional mobile spotlight made from robust ABS plastic with integrated LED technology with very high lighting power
- Extremely bright with 120 LEDs and a power of max. 60 W
- Replaceable lithium-ion rechargeable battery (14,8 V / 5200 mAh)
- Four different light levels:
 25% | 750lm | ca. 12 hours
 50% | 1500lm | ca. 6 hours
 75% | 3000lm | ca. 3.5 hours
 100% | 4500lm | ca. 2 hours
- Base can also be used for hanging
- Lighting units can be swivelled independently of each other
- LED status indication for rechargeable battery capacity
- IP54 / IK07
- Charge time: ca. 3.5 hours

INFORMATION

Product name	HS4500R-DUO
Part No.	1600-0358
EAN-Code	4013674167357
Customs tariff number	85131000000
Product content	Lamp, charger, rechargeable battery pack, operating instructions

Product	176 × 132 × 299 mm / 2295 g
Packing + Product	182 × 160 × 318 mm / 2682 g
Packing Unit	4 (380 × 335 × 335 mm)

