







## **ANSMANN PL130B**

- High-quality and convenient ABS plastic penlight for professional use
- Use of SMD LED technology
- Optimum light output with side-mounted main light or LED in the lamp head
- Brightness: Up to 130 lumens
- Battery life: ca. 7 hours
- Light range up to 16 metres
- Protection: IP20
- Including mounting clip with integrated magnet
- Includes 2× alkaline AAA batteries

## **INFORMATION**

 Product name
 PL130B

 Part No.
 1600-0385

 EAN-Code
 4013674169368

 Customs tariff number
 85131000000

**Product content** PL130B, 2× AAA batteries, operating

instructions

 $\begin{array}{lll} \textbf{Product} & 160\times18\times15~\text{mm} \ / \ 20~\text{g} \\ \textbf{Packing + Product} & 47\times21\times172~\text{mm} \ / \ 42~\text{g} \\ \textbf{Packing Unit} & 16~ [222\times173\times209~\text{mm}] \end{array}$ 

