

LED Spotlights



VT-1977

HIGHLIGHTS :

WATTS



7

EQ. WATTS



45

LUMINOUS



500

BEAM ANGLE



110

Item No	: VT-1977
SKU Code	: 1690
Watts	: 7
EQ Watts	: 45
Base / holder	: MR16
Voltage	: AC/DC:12V,50Hz
Lumen(lm)	: 500
Color Temperature	: 6000K
Beam Angle	: 110
PF	: >0.5
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A+
Certification	: EMC,LVD,ROHS
IP Rating Protection Class	: IP20

Body type	: PLASTIC
Dimmable	: No
Life Time	: 20,000 Hours
Operation Temperature	: -20~50'C
EAN code	: 3800157606974
Unit size	: D:50x50mm
Packing details	: 200
Unit cbm	: 0.000125

PRODUCT FEATURES

- Lasts 20 times longer than Standard Bulbs
- Uses 80% less energy than Standard Bulbs
- Non – Flickering
- Excellent Heat Radiation Efficiency
- Customized exterior for stronger body
- Perfect choice for Exhibition Stands,Hotels, Bars, Commercial & Residential Lighting

[CLICK HERE](#)
FOR OTHER RELATED CERTIFICATES 