


Dismantling Tool

16
30

► **Universal tool with adjustable cutting depth and three types of cut: circular, longitudinal and spiral cut**

- > For dismantling round cable sheaths made of PVC, rubber, silicone or PTFE from 19–40 mm dia.
- > Self-tightening holding lever
- > With knurled nut for cutting depth adjustment
- > Changing from circular to longitudinal cutting by turning the tool body
- > Spiral cutting for removing intermediate pieces
- > Replaceable blade
- > Housing: plastic, impact-proof

 For cables with dia. of between 19 and 40 mm



Setting the tool for circular cut



Setting the tool for circular cut





Precise spiral cut by blade that locks into place



Accurate circular cut



Simple longitudinal cut by handle body which rotates against the limit stop

Article No.	EAN	↔ mm		Stripping capacities mm	⚖ g
16 30 145 SB 	081029	150		19 - 40	140
16 30 135 SB	033349	135		6 - 29	120
16 39 135	027317	Spare blade for 16 30 145 SB / 16 30 135 SB			