

Datasheet **RS Pro A Housing Series**

Specifications Hoods:

Material Colour Surface Locking element Lever type zinc die-cast RAL 7036 powder-coated steel, zinc-plated metal Hoods/Housing seal Limiting temperatures Degree of protection acc. to DIN EN 60 529 for coupled connector NBR -40 °C ... +125 °C **EN**

IP44



Hood, side entry

Hood, top entry

| | Hood | l, side e | ntry | | | Hood, top entry | | | | | | |
|-------------------------------------|------|-----------|------|-----|-------------|-----------------|----|----|-----|-------------|--|--|
| Drawing Dimen- sions in mm | | | | | | | | | | | | |
| | а | b | h | М | Part number | а | b | h | М | Part number | | |
| RS Pro 3A | 28 | 27 | 54.3 | M20 | 1715690 | 28 | 27 | 60 | M20 | 1715689 | | |



Bulkhead-mounted housing



Cable to cable housing, top entry

| | Bulkh | ead-mo | ounted h | nousing | | Surface mounted housing | | | | | |
|-------------------------------------|-------|--------|----------|---------|-------------|-------------------------|----|----|-----|-------------|--|
| Drawing Dimen- sions in mm | | | | | | | | | | | |
| | а | b | с | h | Part number | а | b | h | М | Part number | |
| RS Pro 3A | 41 | 40 | 30 | 27 | 1715688 | 24 | 34 | 57 | M20 | 1715691 | |



Bulkhead-mounted housing, angled



Surface mounted housing, open bottom

| | Bulkh | ead-mo | | Surface mounted housing | | | | | | | |
|-------------------------------------|-------|--------|----|-------------------------|-------------|----|----|----|------|-----|-------------|
| Drawing Dimen- sions in mm | | | | | | | | | | | |
| | а | b | С | h | Part number | а | b | с | h | М | Part number |
| RS Pro 3A | 40 | 28 | 30 | 23 | 1715687 | 58 | 40 | 30 | 24.5 | M20 | 1715692 |