

FEATURES

- Pull torch body to reveal COB LED Work light
- Twisting Flood to Spot control
- Rubberised USB Charging cover
- Rubberised operation switch
- Strong magnet in base

RS PRO LED Torch - Rechargeable 550 lm, 550 lm

RS Stock No.: 176-6030



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS PRO, comes a high quality and great value, 2 in 1 550 lumens flashlight & work light. Constructed out of a high-end black aluminium, a 550 Lumen CREE XPG2 LED for the torch and a 550 Lumen COB LED for the work light, this 2 in 1 flashlight is ensured to be an essential solution for your day to day uses.

General Specifications

Torch Style	Flashlight
Lamp Type	LED
Luminosity	550lm
Range	150m
Beam Type	Focused
Switching Modes	Torch High ON / OFF / Work light High ON / OFF
Light Colour	White; Red
Colour	Black
Case Material	Aluminium
Anti-Corrosive	No
Hazardous Area	No
Applications	Automotive maintenance, Healthcare, Home DIY and Camping

Modes Specifications

Parameters	CREE XPG2 TORCH	COB LED WORK LIGHT	COB RED WORK LIGHT
Light Output	550lm	550lm	45lm
Run Time	3hours	3hours	5hours
Beam Distance	150m	32m	13m



Electrical Specifications

Rechargeable	Yes
Batteries	3.7v 2200mAh Li-ion Rechargeable Battery
Battery Indicator	No
Switch Type	Rubberised Operation Switch

Mechanical Specifications

Length	174mm when not extended , 227mmwhen extended
Width	35mm
Head Diameter	44mm
Weight (with Batteries)	367g

Protection Category

IP Rating	IPX4

Approvals

Compliance/Certifications	RoHS Certificate Of Compliance
Standards Met	ANSI FL1 Standard



