

FEATURES

- Designed with antiroll body
- Flood to spot twist control
- Magnetic base that connects to charging base
- Detachable pocket clip
- An easy to press circular switch

RS PRO LED Torch - Rechargeable 300 lm

RS Stock No.: 176-6035



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS PRO, comes a high quality and great value 300-lumen rechargeable flashlight. Constructed out of a high-end black aluminium and fitted with a CREE XP-G2 300 lumen LED, this small and compact LED flashlight proves to be an excellent solution for your day to day needs.

General Specifications

Torch Style	Pocket
Lamp Type	LED
Luminosity	300lm
Range	100m
Beam Type	Spot to Flood
Switching Modes	High, Low, Medium, Flash ON/OFF
Light Colour	White
Colour	Black
Case Material	Aluminium
Anti-Corrosive	No
Hazardous Area	No
Applications	Automotive maintenance, Healthcare, Home DIY and Camping

Modes Specifications

Parameters	High Mode	Medium Mode	Low Mode / Strobe	Flash ON/OFF / SOS
Light Output	300lm	125lm	35lm	
Run Time	1 hour	2 hours	9 hours	2 hours
Beam Distance	100m	60m	30m	



Electrical Specifications

Rechargeable	Yes
Batteries	3.7V 600mAh Li-ion rechargeable battery
Battery Indicator	No
Switch Type	Circular easy press Switch

Mechanical Specifications

Length	93mm
Width	30mm
Depth	30mm
Weight (with Batteries)	94g

Protection Category

IP Rating	IP44

Approvals

Compliance/Certifications	RoHS Certificate Of Compliance
Standards Met	ANSI FL1 Standard















