

FEATURES

- Ultra slimline and compact body
- The floodlight is made from aluminium and toughened glass
- 115° beam angle
- Adjustable bracket
- The LED bulbs offer a 4000K colour temperature which translates to a cool white light
- An LED luminaire offers up to 90% more energy efficiency than traditional Halogen or incandescent bulbs
- Suitable for outdoor use
- Ideal for industrial and commercial applications, as well as home use

RS PRO LED Floodlight, 150 W, 13500 lm, IP65 220 → 240 V ac

RS Stock No.: 176-8533



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS Pro 300W LED Floodlight has an ultra slim line body for an aesthetically pleasing look and discrete installation. With a small form factor and it being extremely light, this makes for an effortless install. Also this floodlight is built around an IP65 protection rating so makes ideal use for indoor or outdoor use.

General Specifications

Floodlight Type	LED Floodlight
Luminosity	9000lm
Lumen Efficiency	90 Lm/W
Range	REX Slim
Light Colour	Cool White
Colour Temperature	4000K
Beam Angle	115°
Case Material	Aluminium
Housing Colour	Black
Applications	Warehouses, Car Parks, Walkways, Construction areas, Parks and gardens, Home security

Electrical Specifications

Wattage	100W
Voltage	220V to 240V ac
Frequency Range	50Hz to 60Hz
Lamp Type	Fixed LED
Dimmable	No
Life Hours	30000h

Mechanical Specifications

Dimensions	281.6mm x 38mm x 320.9mm
Height	320.9mm
Width	281.6mm
Depth	38mm

Protection Category

IP Rating	IP65
IK Rating	IK08

Approvals

Compliance/Certifications	EN61340
----------------------------------	---------



