

## FEATURES

- HDMI to DVI-D cable
- Male-to-male connectors
- Suitable for digital not analogue signals
- Supports a maximum resolution of 1920x1200
- Dual-link for higher bandwidth
- Internal wire size of 28 AWG
- 10 metres long
- Black PVC sheath for protection
- Gold-plated connectors to withstand corrosion
- Screw closure for a secure connection

# RS PRO 1920 x 1200 - HDMI to DVI-D Cable, Male to Male- 10m

RS Stock No.: 182-8572



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This HDMI to DVI-D male-to-male cable connects an HDMI-equipped source device such as a laptop, Blu-ray player or games console to a DVI-D compatible display. Some common examples of these include HDTVs, computer monitors and projectors.

### General Specifications


<b>Cable Type</b>	HDMI to DVI-D
<b>Connector A</b>	Male HDMI
<b>Connector A Gender</b>	Male
<b>Connector A Type</b>	HDMI
<b>Connector B</b>	Male DVI-D
<b>Connector B Gender</b>	Male
<b>Connector B Type</b>	DVI
<b>Maximum Resolution</b>	1920 x 1200
<b>Outer Sheath Material</b>	PVC
<b>Sheath Colour</b>	Black
<b>Applications</b>	Computer Monitors, Digital Broadcasting, Blu-Ray Players, Gaming Consoles

### Mechanical Specifications

<b>Length</b>	10m
<b>Wire Gauge</b>	28 AWG
<b>Outer Diameter</b>	7.3mm

### Approvals

<b>Compliance/Certifications</b>	CE, REACH, RoHS Compliant
----------------------------------	---------------------------



HDMI(M)	1	3	2	4	6	5	7	9	8	10	12	11	17	18	15	16	19	64
DVI(24+1)P	2	1	3	10	9	11	18	17	19	23	24	22	15	14	6	7	16	64
	对绞		地	对绞		地	对绞		地	对绞		地	30AWG		30AWG		64	SHELL

1. CABLE: 28AWG,UL20276,AL+B-FOIL,[(#28\*1P+D+FAM)\*4PCS+#28\*1P+#28\*3C]+AM+B, BLACK COLOR,OD=7.3±0.2mm,PVC JACKET.(double shielded )
2. LENGTH
3. CONNECTORS: HDMI(M)\*1PCS(BLACK INSULATOR),DVI(24+1)P\*1PCS(BLACK INSULATOR)(全为镀金壳)
4. MOLD: MOLDING TYPE.
5. SCREW: #4\*40 INCH SCREW\*2PCS.(镀金螺丝)
6. CONTACTS