

FEATURES

- Black RJ45 (8 way)
- 2 Ports Socket to Socket
- UTP Shielded coupler
- PBT Material for Durable design
- Phosphor bronze contacts with gold over nickel plating
- Dimensions: 20.55 x 14.48 x 26.98 mm

RS PRO RJ45 Modular Coupler, 2 Port, Shielded

RS Stock No.: 186-3111



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Ethernet Couplers



Product Description

From RS PRO, this RJ45 Modular Coupler enables RJ45 connector plugs and cable assemblies to be patched together straight through a patch panel or blank faceplates. This shielded modular inline coupler has a durable design and can easily press-fit into pre-cut panels. This is ideal for those who need a custom network architecture solution.

General Specifications

Туре	Modular Coupler
Interface Type	RJ45
Number of Ports	2
Shield Type	Shielded
Wiring Configuration	Straight Through
Colour	White
Contact plating	Gold Over Nickel
Housing Material	Thermoplastic UL 94V-0
Contact Material	Phosphor Bronze
Application	RJ45 connectors and cables are typically used for internet connections, forming either local area (LAN) or wide area (WAN) networks. For workspaces where Wi-Fi is restricted, or when a more dependable hardwire connection is required, this adapter allows you more mobility around an Ethernet connection. For connecting personal computers to modems and network architecture, this adapter is ideal

Mechanical Specifications

Length	18.54mm
Width	21mm
Depth	27.46mm



Approvals





