


## Datasheet Stock No. 1863124 RS PRO Connector Assembly







All dimensions are in mm.

## General SpecificationRated Operational Voltage30 VCurrent Rating4AInsulation Resistance>= 10Temperature Range-25°C

501	
4A	
>= 100 MΩ	
-25°C +75°C	
IP67	

## **Material Specification**

Degree of Protection

•	
Grip Material	PU
Contact	Cu-Zn
Contact Plating	Gold Plated
Contact Carrier	Nylon 66
Grip Colour	Black
Coupling Nut	Brass Nickel-Plated

## **Cable Specification**

•	
Cable Length-L	2 m
Cable Type	4 Core PUR Multi Strand
Sheath Colour	Black
Cross Section of Wire	0.34 sq. mm
Core Dia	1.3 mm
Cable Dia	4.9 ± 0.1 mm
Termination	Partially Stripped

Specifications are subject to change without notice.

Pin Assignment

