

FEATURES

- 250 Lumen white Cree LED light
- Rechargeable via USB (micro -USB cable included)
- LED battery and charging indicator
- LED colour temperature 6500k
- Super lightweight at only 95g
- Allows you to continue working hands free

RS PRO LED Head Torch - Rechargeable 250 Im

RS Stock No.: 186-4621



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Introducing the rechargeable compact LED head torch from RS PRO, a lightweight high quality head torch ideal for use in a wide range of applications that require a source of light. This versatile torch offers a variety of modes to accommodate for numerous applications including a standard torch light source with an LED colour temperature of 6500k, SOS and strobe.

General Specifications

Torch Style	Head Torch
Lamp Type	LED
Luminosity	250lm
Beam Type	Spot; Flood
Switching Modes	High, Low, Medium
Anti-Corrosive	No
Hazardous Area	No
Applications	Automotive maintenance, Healthcare, Home DIY and Camping

Modes Specifications

Parameters	Spot Beam High Mode	Spot Beam Medium Mode	Spot Beam Low Mode / Strobe	sos
Light Output	250lm	76lm	12lm	
Run Time	6hour	12hours	93 hours	17hours
Beam Distance	66m	38m	14m	



Modes Specifications

Parameters	Flood Light High Mode	Flood Light Low Mode / Strobe
Light Output	52lm	16lm
Run Time	16hour	53hours/116hours
Beam Distance	10m	5m

Electrical Specifications

Rechargeable	Yes
Plug Type	Micro USB Cable
Batteries	Rechargeable High Quality 3.7VmAh Li-polymer
Charging Time	Approx. 3hours (Turn product off when charging)
LED Charging Indicator	Red-Charging, Green-Fully charged
Battery Indicator	Yes

Mechanical Specifications

Length	62mm
Width	47mm
Depth	37mm
Weight (with Batteries)	95g

Protection Category

IP Rating IPX6

Approvals

Compliance/Certifications	RoHS Certificate Of Compliance









Torches

