

### **FEATURES**

- Hard touch & soft touch switch
- Convex lens for smooth long beam
- Strobe & safety beacon modes offering versatility
- Tough aircraft grade anodised aluminium construction offering excellent durability

# **RS PRO LED Torch 2600 Im**

RS Stock No.: 186-4624



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

Introducing the waterproof LED torch from RS PRO, a high power flashlight with zoom feature ideal for creating a bright light source in a wide range of environments. The torch features a powerful 2600 lumen white Cree LED bulb with 5 light settings including high, mid, low, strobe and safety beacon, offering a versatile flashlight suitable for a multitude of applications.

### **General Specifications**

Lamp Type	LED
Luminosity	2600lm
Range	400m
Beam Type	Flood to Spot
Switching Modes	High, Low/Strobe, Medium
Case Material	Aluminium
Anti-Corrosive	No
Drop Resistance	1m
Hazardous Area	No
Applications	Automotive maintenance, Healthcare, Home DIY and Camping

#### **Modes Specifications**

Parameters	High Mode	Medium Mode	Low Mode / Strobe
Light Output	2600lm	900lm	260lm
Run Time	2hours	2.5 hours	9 hours/2hours
Beam Distance	400m	322m	219m



# **Electrical Specifications**

Rechargeable	No
Batteries	9 x LR6 AA 1.5V Alkaline Panasonic Batteries
Battery Indicator	No

# **Mechanical Specifications**

Length	240mm
Depth	54.4mm
Weight (with Batteries)	613g

# **Protection Category**

IP Rating	IP67

# **Approvals**

Compliance/Certifications	RoHS Certificate Of Compliance
---------------------------	--------------------------------



