

FEATURES

- Rechargeable via micro-USB cable
- Compact design ideal for working in tight spaces
- Super strong magnetic base
- Rotating nylon hanging hook allowing you to work hands free

RS PRO LED Inspection Light - Rechargeable 700 Im

RS Stock No.: 186-4628



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Introducing the compact LED inspection torch from RS PRO, a lightweight yet durable torch ideal for lighting up dark spaces with precision in a range of environments. The versatile light features two brightness settings including flashlight and floodlight. This compact inspection light is housed in a durable ABS and rubber enclosure with IK07 and IP54 protection, ensuring the torch is protected against accidental shock impact and dust or water ingress

General Specifications

Torch Style	Inspection Torch	
Lamp Type	LED	
Luminosity	700lm	
Beam Type	Flood	
Switching Modes	Flashlight , Floodlight	
Light Colour	White	
Case Material	ABS, PC	
Anti-Corrosive	No	
Hazardous Area	No	
Applications	Automotive maintenance, Healthcare, Home DIY and Camping	

Modes Specifications

Parameters	Flashlight Mode	Floodlight High Mode	Floodlight Low Mode / Strobe
Light Output	175lm	700lm	350lm
Run Time	10hours	1hour 40mins	4hours 25mins



Electrical Specifications

Rechargeable	Yes
Plug Type	1m Micro USB Cable
Batteries	Rechargeable High Quality 3.7VmAh Li-polymer
Charging Time	Approx. 4hours
LED Charging Indicator	Red-Charging, Green-Fully charged
Battery Indicator	No

Mechanical Specifications

Length	190mm
Width	33.6mm
Depth	56mm
Weight (with Batteries)	210g

Protection Category

IP Rating	IP54

Approvals

Compliance/Certifications	RoHS Certificate Of Compliance
---------------------------	--------------------------------





