



ENGLISH

Datasheet

RS PRO SW-615RS 5 Port Gigabit Hardened Ethernet Switch

Stock Number: 189-0536



Specifications:

- Power Consumption: 3.6W Max:
720mA@+5VDC/120mA@+30VDC
- Power Supply input: Unregulated +5V to +30Volts DC, reverse polarity protection
- Operating Temperature: -40°C to +80°C/-40°F to +176°F
- Ethernet Ports: 5 x RJ45 jack, 1 Gigabit autosensing, crossover auto sensing (Auto MDIX)
- Unmanaged Gigabit Ethernet
- Housing: IP-20 rated metal case with Easy Wire Removable screw terminal block
- Weight: 0.27 kg
- Dimensions: 99x95x29 mm

Features:

- 5 Port Gigabit Ethernet Switch
- Redundant dual power inputs: +5V to +30V DC
- Hardened metal case with integral DIN mount
- No software required - Simply plug in and connect
- Industrial temperature range

