

	10	9		8		7	Ģ		5		4		
F	MAT'L NO.	ENG NO.	MAT'L NO.		ENG NO.	PERMA-SEAL	WIRE 3	"A" MIN		"B" Ø MAX		"C" MAX	"H" ± .
			ΤΑΡΕ Μ	OUNT	TAPE MOUN	T COLOR	AWG	A	IVIIIN			CIVIAX	П т.
	191640013	SAA-22-18	191640014		SAA-22-18T	SAA-22-18T SAA-22-18T		.185 (4.70)		.280 (7.11)		1.55 (39.4)	.767
	191640044	SBB-16-14	191640	0045	SBB-16-14T	SBB-16-14T	16 - 14	.195	(4.95)	.308 (7.82	2)	1.55 (39.4)	.765
	191640056	SC-12-10	191640	0057	SC-12-10T	SC-12-10T	12 - 10	.275	(6.99)	.383 (9.73	3)	1.80 (45.7)	.800
	191640079	SD-354		· _			8	.300	(7.62)	.448 (11.3	88)	2.05 (52.4)	-





NOTE(S):

C

В

A

1 INSULATION MATERIAL: HEAT SHRINKABLE

TUBING WITH HOTMELT INNER LINER. (SEE CHART FOR COLOR).

2 SEAMLESS TIN PLATED COPPER TERMINAL.

3 PRINTED TEXT IN BLACK APPROX. .12(3.0) HIGH

4. PARTS ARE RoHS COMPLIANT.

	4	3			2			1	-	
	"C" MAX	"H" ± .020	(0.51)	"D	" MIN					
	1.55 (39.4)	.767 (19	.48)	.059	9 (1.50)				F	
	1.55 (39.4)	.765 (19	.43)	.09	1 (2.31)					
	1.80 (45.7)	.800 (23	.32)	.139	9 (3.53)					
	2.05 (52.4)			.16	5 (4.19)					
									E	
	Ø"D" MIN V		▲ "H" ↓		MOUNTIN	GLOC		N	D	
1									С	
7	NCTIONAL THIS DRAWING CONTAINS INFO YMBOLS DIMENSION UNITS SCALE DIMENSION UNITS SCALE INCH/MM 1:1 GENERAL TOLERANCES (IN ESS OPECIEIES)	TMATION THAT IS PROPRIETA CURRENT REV DESC: "1 (.025)						TTEN PERMISSION	B	
	Minimum Minimum Image: Specified of the specified	EC NO: 740839 DRWN: DEANNM1 2023/03/02 CHK'D: JMACNEIL 2023/03/11								
	1 PLACE ± ± 0 PLACES ± ±	APPR: JMACNEIL INITIAL REVISION: DRWN: BENDERLE		2023/03/11	DOCUMENT NUMBER	-	DOC TYPE DOC PART REVI			
	ANGULAR TOL ± ° DRAFT WHERE APPLICABLE	APPR: RDEROSS	DRAWING	2002/04/03	SD-191	64-017 CUSTOMER	PSD	001 F3	A	
	MUST REMAIN WITHIN DIMENSIONS		B-SIZE	19164	SEE CHART	GENERAL I	MARKET	1 OF 1]	
	4	3			2			1		

DOCUMENT STATUS F	P1 RELEASE DATE	2023/03/11 17:59	10				WITHIN DIMENSIONS	
FORMAT: Eng-lega-master-tb-prod-B REVISION: E DATE: 2020/01/14	9		8	7	6	5	4	