

Honeywell Sensing and Control



Search

192-501 DEV-A01
 ([Home](#) : [Products](#) : [Sensors](#) » [Temperature Sensors](#) » [Discrete Thermistors](#) » 192)

narrow your search

- Products**
- Controls Monitoring and Lighting (286)
 - Machine Safety (1727)
 - Sensors (6004)
 - Switches (9781)
 - Wireless (45)
- Technology**
- Control and Instrumentation (988)
 - Electromechanical (9307)
 - Magnetic (541)
 - Platinum thin film (56)
 - Thick Film (1409)
 - More...



192 Series, Uni-Curve with bare leads and epoxy, 500 Ohm resistance, ±0.5 °C [0.9 °F] tolerance, 25/85 BETA = 3348

Actual product appearance may vary.

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) | [Specs](#) | [Documentation](#) | [Application Notes](#)

Product Specifications

Availability	Global
Resistance	500 Ohm
Tolerance	±0.5 °C [0.9 °F]
Accuracy	0 °C to 70 °C [32 °F to 158 °F]
Beta	3348
Operating Temperature	-60 °C to 150 °C [-76 °F to 302 °F]
Diameter	2,413 mm [0.095 in]
Termination Material	32 Gauge tinned copper, alloy 180
Lead Length	38,1 mm [1.50 in]
Time Constant in Air	15.0 s
Dissipation Constant	0,75 m/W°C
Series Name	192

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



[Wireless Web Site WGLA and WPMX XYR6000™](#)

[find out more](#)

white papers

- ▶ [Wireless Switches Offer Unlimited Benefit](#)
- ▶ [Basic Switches Are Not Created Equal](#)
- ▶ [Applying Precision Switches](#)
- ▶ [Sensors for Medical Devices](#)
- ▶ [New Ways to Measure Torque](#)
- ▶ [Choosing Safety Switches](#)
- ▶ [Specifying Hour Meters](#)

Need help?

[Click here to contact us](#)

contacts

- ▶ [Customer Service](#)
- ▶ [Technical Support](#)
- ▶ [Global Sales & Service](#)
- ▶ [View Site Demo](#)
- ▶ [Site Comments?](#)

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



▶ [Meet Dr. Larry](#)

my links

- ▶ [Login to iCOM](#)
- ▶ [Login to Rep/AD Portal](#)
- ▶ [Login to Digital University](#)

News Center

- ▶ [HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER](#)
- ▶ [HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION](#)
- ▶ [HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO](#)
- ▶ [HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION](#)
- ▶ [HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT](#)

MICRO SWITCH Anniversary site