

# ROLINE DesignSecure 2000

<b>Product No.</b>	19.40.1220
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	19.40.1220
<b>EAN (single piece)</b>	7611990976744



- Compact designed UPS in futuristic design
- For Workstations and PCs
- LineInteractive UPS
- AVR (Automatic Voltage Regulation)
- Digital status display
- Integrated overvoltage protection
- Telephone/Modem connections
- USB Port for advanced Power Management Software (incl. in content of delivery)
- EMI/RFI Noise Filter
- Dimensions (HxLxW) 168 x 105 x 334 mm
- Weight: 6.3 kg
- Backup Time: up to 4 Minutes

## Technical specifications

Manufacturer	ROLINE
Product group	UPS
Product type	UPS Line Interactive
Colour	black /silver
Scope of delivery	UPS, Software, Cable Set
Classification (IEC 62040-3)	VI-SS-333
UPS technology	Line Interactive

Power class	2000 ... 3000 VA
Output (VA/W)	2000 / 1200
Backup time	2 min
Backup time full/half-load	2 / 4 min
Dimensions (HxWxD)	192 x 130 x 382 mm
Mounting form	Turm
Voltage (input)	230 V
Voltage (output)	230 V
Output voltage regulation	yes
Frequency	50 Hz
Connector type (input)	cold connector IEC320 C14
Outputs	6
Connector type (output)	6 cold connector IEC320 C13
Phase in/output	230V/230V / 50Hz
Over current protection	EMI,- RFI-Filter
Max. quantity of delay expansion units	0
Delay expansion unit	--
Slots for adapter card	0
Slot for adapter card	--
Interface	USB
USB 2.0 Interface	Yes
Hot swap batteries	No
Bypass	No
Additional over current protector	Telephone/Fax
Activity	Display
Activity LED	--
Activity Display	yes

incl.Management Software	Windows
Internal cooling	Passive
Ambient temperature	0-40 °C
Height	192 mm
Width	130 mm
Depth	382 mm
Weight	16 kg
Height of packaging (single piece)	330 mm
Width of packaging (single piece)	270 mm
Depth of packaging (single piece)	500 mm
Package weight (single piece)	16.171 kg

### Backup Time

Capacity (VA / W)	minutes
200/120	65
400/240	28
600/360	14
800/480	9,5
1000/600	7
1200/720	5
1400/840	4
1500/900	3,5
1600/960	3
1800/1080	2,5
2000/1200	2