

Han-Eco 16B-HSE-for DL-M25



Part number	19 43 016 0526
Specification	Han-Eco 16B-HSE-for DL-M25
HARTING eCatalogue	https://b2b.harting.com/19430160526

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco [®] B
Type of hood/housing	Hood

Version

Size	16 B
Version	Side entry
Cable entry	1x M25
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Material properties

China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984 EN 45545-2 Fire protection on railway vehicles
CE	Yes

Commercial data

1
149 g
Germany
85389099
5713140178809
27440202 Shell for industrial connectors