



## **Datasheet**

**RS PRO Panel Heater** 

with integral 7 day 24 hour LCD electronic timer and controls

Stock number: 196-2386, 196-2387, 196-2388

EN



The 24/7 Panel Heater connects directly to the permanent electricity supply

offering two heat output settings depending on your heating needs. The timer option allows user to select one of 12 pre-set programmes or create a customised 'DIY' heating programme. Wall fixtures are included.





## **Key Features**

- Silent in operation
- Lot 20 compliant
- High efficiency of airflow with over 95% of used energy creating heat
- User friendly LCD display screen
- 12 pre-set programmes available
- 1 user defined programme available
- Program and real-time clock memory function
- Thermostat for temperature setting (5°C-30°C)
- Adjustable temperature in Normal and Economic modes
- 24 hour On/Off Timer
- Anti-frosting function
- Ionizer function
- Child safety lock
- Over-heat safety protection
- IP24 rated

## **Technical Specifications**

RS Stock Number	196-2386	196-2387	196-2388
Power	1000W	1500W	2000W
Colour	White	White	White
Max Heat output	1000W	1500W	2000W
Heating area	10-13m <sup>2</sup>	15-18m <sup>2</sup>	20-23m <sup>2</sup>
Voltage	230-240V (50Hz)		
Approvals	CE, EMC, LVD, RoHS, ERP		
Size (HxWxD)	440 x 455 x 125mm	440 x 615 x 125mm	440 x 775 x 125mm
weight	4kg	5.1kg	6.5kg



