

## Han 24EMC/B-HTE-M40 (HT)



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 62 824 0428  |
| Specification      | Han 24EMC/B-HTE-M40 (HT)  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19628240428">https://b2b.harting.com/19628240428</a> |

### Identification

|                          |  |
|--------------------------|--|
| Category                 | Hoods/Housings                                       |
| Series of hoods/housings | Han <sup>®</sup> EMC/B<br>Han <sup>®</sup> High Temp |
| Type of hood/housing     | Hood   |
| Type                     | High construction                                    |

### Version

|                      |  |
|----------------------|--|
| Size                 | 24 B                                       |
| Version              | Top entry                                  |
| Cable entry          | 1x M40                                     |
| Locking type         | Double locking lever                       |
| Field of application | Hoods/Housings for higher EMC requirements |

### Technical characteristics

|  |   |
|--|---|
| Limiting temperature                   | -40 ... +125 °C<br>-40 ... +200 °C With Han <sup>®</sup> High Temp components |
| Degree of protection acc. to IEC 60529 | IP65<br>IP66  |
| Type rating acc. to UL 50 / UL 50E     | 4<br>12   |

### Material properties

|                         |                    |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing)  | Uncoated           |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| Colour (hood/housing)                | Unpainted     |
| RoHS                                 | compliant     |
| ELV status                           | compliant     |
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Yes           |

## Specifications and approvals

|           |  |
|-----------|--|
| Approvals | DNV GL   |
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| CE        | Yes  |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 246.2 g                                  |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |