



4W

VT-1980 4W G45 FILAMENT BULB COLORCODE:2700K E27

Equivalent
40W

Lumens
400

Beam Angle
300

Dimensions
45 x 75mm

Warm White
SKU:4306



2 YEARS
WARRANTY



Technical Information

Instant Start: 0-100% in lt1s

EQ-WATTS: 40

Watts: 4

Lumens: 400

Holder Type: E27

Shape: G45

Beam Angle: 300

Unit Color: TRANSPARENT

Body Type: GLASS

Energy Rating: A+

Long life: 20,000 Hours

LED Chip Type: FILAMENT

IP Rating: IP20

Dimmable: No

Warranty (Years): 2

PF: >0.4

CRI: >80

Operation Temperature: -25 to +50°C

Input Power: AC:220-240V,50Hz

Sensor Compatibility: Yes



Features

- ✓ Uses 80% less energy and lasts 20 times longer than Standard Bulbs
- ✓ LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- ✓ Stable LED Filament technology for extended lifespan
- ✓ Glass body available in Clear, Frost and Amber Shades
- ✓ High luminous efficacy & Low Power consumption
- ✓ Excellent Power factor & Integrated IC driver
- ✓ Crafted with Splendid filament designs
- ✓ Multiple Configurations for enriched antique vintage ambiance
- ✓ Excellent Heat Radiation Efficiency
- ✓ No Flickering - No UV Radiation - No Mercury
- ✓ Dimmable & Non Dimmable options
- ✓ Broad Range of holders (E27, E14, B22) & Shapes (Candle, Globe, A60, Candle Flame, ST64, T30)
- ✓ Application - Residential Lighting, Commercial Lighting, Decorative, Living Room, Lounge, etc.

Packaging

Unit Details

Length(Box)mm	52
Width(Box)mm	52
Height(Box)mm	85
Unit CBM	0.0002

Listing Details

EAN Code	3800157600330
Commodity Code	9405403990



Master Box Packaging

Master Box Qty (Pcs Per Carton)	100
---------------------------------	-----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES