

FILAMENT BULBS

ITEM NO: VT-1986D; WATTS: 4W



Item No:	VT-1986D
SKU Code	4365:3000K
Type	Candle
Base	E14
Real Watts	4W
EQ. Watts	40W
Voltage	220-240V
Input Frequency	50Hz
Input Efficiency	100lm/w
Lumen(lm)	400lm
PF	>0.4
CRI	>80
Color Temperature	3000K
Beam Angle	300'D
LED Chip	Filament
Driver	Constant current dimming driver
Protection Class	IP20
Body Material	Glass
Dimmable	Yes
Unit size	37mmx100mm
Life Time	20000hrs
Operation Temperature	-25 ~50'C
Applicable Environment	Indoor Lighting, Used in Home down light, Stairwell lighting.