

VALUE USB Wall Charger, 3-Port, (2x C+ 1x A), 65W, GaN

Product No.	19.99.1096
Manufacturer	VALUE
Manufacturer No.	19.99.1096
EAN (single piece)	7630049623415



1-port USB charger, 1x Type A with maximum 12W for powering a smartphone/tablet, external SSD/HDD or other devices

- For charging or as a power supply from a device via its USB input
- Perfect supplement for your Wireless Charger, as the scope of delivery often does not include plug-in power supplies
- Suitable, for example, for smartphone/tablet, external SSD/HDD enclosures and other devices
- Charger with one USB Type A socket
- Matt black PVC housing and Euro flat plug

Technical data

- Plug-in power supply with 3x USB output, type (2x C+ 1x A) socket
- Input voltage: 100 - 240V AC, 50 - 60Hz
- Output voltage:
 - USB-C 1: PD65W (5V 3A / 9V 3A / 12V 3A / 15V 3A / 20V 3.25A)
 - USB-C 2: PD65W (5V 3A / 9V 3A / 12V 3A / 15V 3A / 20V 3.25A)
 - Output A: 30W (4.5V 5A / 5V 4.5A / 9V 3A / 12V 2.5A / 20V 1.5A)
- USB: C1+C2+A: PD45W(C1) + 5V 3.6A(C2+A)
- Output power: 65W
- Dimensions: 50 x 30 x 93 mm

Advantages of GaN technology

- GaN or gallium nitride - crystalline material with more advantageous properties compared to silicon

- Powerful, efficient power supply
- Enables more compact charger design
- Low heat generation
- Allows a higher density of electronic components

Technical specifications

Manufacturer	VALUE
Product group	Voltage converter
Product type	USB charger
Colour	black
Input	100-240 VAC
Output	USB-C 1: PD65W (5V 3A / 9V 3A / 12V 3A / 15V 3A / 20V 3.25A)
Output	65W
Dimensions (HxWxD)	50 x 30 x 93 mm
Output connector	2x USB Type C F, 1x Type A
Supported charging technology	GaN
Height	50 mm
Width	30 mm
Depth	93 mm
Weight	119 g
Height of packaging (single piece)	20 mm
Width of packaging (single piece)	40 mm
Depth of packaging (single piece)	40 mm
Package weight (single piece)	0.02 kg