

CLAY DESICCANTS

20-053-xxxx

Product specifications

Material:	Bentonite clay
Appearance:	Grey granules in a white bag
Bag:	Non-woven with dissipative coating
Unit weight:	35 grams
Using temperature:	Up to 50°C
Moisture:	Efficient from 15% to 50% HR
Moisture absorption:	5.9 gram/unit of H ₂ O at 20% HR; 6.8 gram/unit @ 40% HR
ESD protection:	Surface resistance (bag) <10 ¹¹ Ω
Reactivation:	120°C (245°F) during 16 hours
Conservation:	Store away from moisture
Packaging:	Packed in moisture barrier bag
Standard compliance:	EN 61340-5-1 MIL-D-3464E



Features and Part Number

Part number	Unit	Quantity per box	Pouch size (mm)
20-053-0002	1/18 unit (2 grams)	2000	70 x 25
20-053-0006	1/6 unit (6 grams)	1000	70 x 60
20-053-0012	1/3 unit (12 grams)	1000	75 x 60
20-053-0017n	1/2 unit (17 grams)	1000	85 x 75
20-053-0035	1 unit (35 grams)	400	102 x 91
20-053-0070n	2 units (70 grams)	250	140 x 102
20-053-0140	4 units (140 grams)	100	150 x 91
20-053-0280n	8 units (280 grams)	60	142 x 135
20-053-0560	16 units (560 grams)	25	210 x 135

Options

Other sizes, weights available

Possible to pack the dessicants in a tin box

Dessicants are also available in silica gel