



Datasheet

RS PRO Precision Cutter (Slim Head)



EN



RS PRO slim head precision cutters are ergonomically designed bi-material pliers which offer high performance for all-day use. Featuring an asymmetric handle profile for increased comfort and less fatigue over long periods of use, the grips also have finger guards integrated into the design to prevent slipping. Ideal for a variety of precision applications where component handling and wire manipulation are common. The cutting jaws are redesigned to feature a slim head for improved access in constricted spaces and for working with smaller components.

Product features:

- Asymmetric grip profile fits the contours of the hand for improved ergonomics
- Bi-material handle for comfortable working all day long
- High leverage pliers offering high performance
- Hot drop forged, hardened and tempered steel
- Induction hardened, precision milled cutting edges
- Screw joint design
- Integral springs to return handles to open position
- For cutting soft and medium hard wire
- Slim head for working in very confined spaces

RS CODE NO	 mm	L mm	 gr
2006026	1.0	140	78



Attributes

Cutting Capacity:	1.0 mm
ESD Safe	N
Height Safe:	N
Jaw Depth:	12 mm
Jaw Length:	24 mm
Material::	Sheet Steel
Non Sparking:	N
Overall Length:	140 mm
Overall Width:	55 mm
VDE/1000V Approved:	N