

SPECIFICATION

RSPRO-H24



3xAAA COB LED Headlight

Technical Data

350 Lumen COB LED with white and red LED modes Dual button design Strobe functions (white & red) 45° rotating head Adjustable headband Super lightweight at only 59g IPX6 water resistant Im impact resistant

Product Size: 63×35×45mm

Product Weight: 59g not including batteries **Battery:** 3 × AAA Alkaline Batteries (included)

Operation

Right Button = WHITE:- High > Mid > Low > Strobe > Off

Left Button = RED:- High > Strobe > Off

MODE	31/2		0
WHITE - HIGH	350 lm	22 m	3 hrs
WHITE - MID	100 lm	12 m	9 hrs
WHITE - LOW	10 lm	4 m	97 hrs
WHITE - STROBE			100 hrs
RED - HIGH	30 lm		5 hrs
RED - STROBE			120 hrs





2 Light Sources







45° Rotating Head Angle



IPX6 Water Resistant

