

SPECIFICATION

RSPRO-F27R



Super Bright USB Rechargeable Flashlight

Technical Data

6000 Lumen white 30W COB LED
Tough aircraft-grade aluminium construction
Power Bank feature for charging devices
Easy twist flood-to-spot focus
White daylight 5500k colour temperature
Flawless domed lens for smooth wide beam spread
Glow-in-the-Dark reflector
Easy press rubberised switch on torch body
Switch also serves as charging indicator light

Safety wrist strap included
Features closed-loop temperature control and smart power control IP67 dust & water proof
Im impact resistant

Product Size: Ø57.3 × Ø33 × 266 mm **Product Weight:** 653.5g (including battery)

Batteries: 7.4v 26650 5000mAh Li-ion Battery Pack (included)

Operation

Short Press from off:- High > Medium > Low > Off Long Press from off:- Low > Medium > High > Off Double click the switch (from Off or any mode) to activate Strobe If left in any mode for 8+ seconds, the next press will turn off.

MODE	314		0
HIGH	6000 lm	191 m	3 hrs
MEDIUM	1200 lm	86 m	7 hrs
rom	60 lm	20 m	50 hrs
STROBE			2 hrs













IP67 Dust & Water Proof



USB Power Bank Output: 5v



USB Charging Cable Inc.

