## Extraction arms 3470

Diameter, mm	Arm Ø 60
Measure/arm part, mm	350 / 230 / 700
Total measure, mm	1280



Art. number	Description
FT-3470	Extraction arm with one joint, wall from top and air valve.



## Extraction arm 3475

Diameter, mm	Arm Ø 60
Measure/arm part, mm	350 / 475 / 475 / 230 /105-235
Total measure, mm	1635-1765



Art. number	Description
FT-3475	Extraction arm with three joints, horizontal link, table bracket, P nozzle and air nozzle.



## Flexible hose/arm



Art. number	Description
0F05	Flexible, adjustable arm 500 mm incl. connection (female) in both ends.
0F07	Flexible, adjustable arm 700 mm incl. connection (female) in both ends.
0F10	Flexible, adjustable arm 1000 mm incl. connection (female) in both ends.
0F15	Flexible, adjustable arm 1500 mm incl. connection (female) in both ends.
0F20	Flexible, adjustable arm 2000 mm incl. connection (female) in both ends.

