

#### **FEATURES**

- LCD display with automatic backlight.
- Detect opens, shorts, miswires and split pairs on twisted pair cabling.
- Displays graph wiremap, opens, shorts, miswires, split pairs and remote ID numbers all on one screen.
- Identify remote ID number on one pair only.
- Measures cable length.
- Using multiple remote ID numbers up to 8 locations.
- Auto power off.
- Low battery detector.

# **RS PRO LAN Cable Tester**

RS Stock No.: 205-0084



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

# **LAN Cable Tester**



#### **Product Description**

- Connection map test: discontinuity, short circuit, incorrect connection, split pairs
- Tests CAT5, CAT6 cables
- Tests UTP, STP cables

## **General Specifications**

Model Number	
Cable Category	CAT5, CAT6
Cable Types	UTP, STP
Test Connectors	Shielded 8-pin modular jack (RJ45)
Wire Map Test	Detects opens, shorts, miswires, split pairs
Length test	up to 255 m (836 ft)
Length Accuracy	± 10%+1.0m (3 ft)
Measuring resolution	0.1m
Remote ID	Can be operated up to 8 locators.
	Optional Accessories: Remote ID(2) to ID(8)
Functions	Auto Backlight, Low Battery Indicator, Auto Power Off

#### **Electrical Specifications**

Power Source	Battery
Battery Type	9V
Battery Included	Yes
Battery Life	Approx. continuous testing 200 times
Plug Type	RJ45 socket

#### **Mechanical Specifications**

Dimensions	156mm x 73mm x 35mm
Length	
Width	
Height	
Weight	170g (with battery)

## **Operation Environment Specifications**

Operating Humidity Range	Below 80% RH
Operating Temperature Range	5°C ~ 40°C
Storage Humidity Range	Below 70% RH
Storage Temperature Range	-10°C to 60°C

# **LAN Cable Tester**



# **Approvals**

Compliance/Certifications	CE
Declarations	Manufacturer Conformity

ACCESSORIES INCLUDED WITH LAN Cable Tester
User's manual x1, 9V AAA battery x1, CAT5 STP Cable x1, Remote ID (1) x1

OPTIONAL ACCESSORIES: remote ID (2) to ID (8)