

**Datasheet** 

Stock No: 208-6040

### **ENGLISH**

# RS Pro PUR Tyred Wheel, 350kg



#### **Product Details:**

## Polyurethane Tyre, Heavy Duty Cast Iron Wheel, PCB Series

- Cast polyurethane tyre, hardness Shore A95
- Cast iron hub
- Temperature range -30°C to +80°C

#### **Industrial - Polyurethane Tyre**

Polyurethanes have very high load capacity, abrasion and tear resistance, soft ride and chemical resistance. Temperature range: -30 to + 90°C.

### **Specifications:**

Load Capacity: 350kg
Tyre Type: Solid
Tyre Material: PUR

Hub Material: Cast Iron

Features: Abrasion Resistant, Corrosion Resistant

Hub Bearing Type: Double Ball Race

Wheel Diameter: 100mm
Wheel Width: 40mm
Bore Diameter: 15mm
Bore Length: 47mm