## ROLINE FO Jumper Cable 50/125µm OM4, LSH/LC, UPC Polish, LSOH, violet, 1.0 m

Product No.
Manufacturer
Manufacturer No.
EAN (single piece)

21.15.9471 ROLINE 21.15.9471 7611990150540





## High-quality fibre optic cables with the high protective, secured LSH connection on one side and LC plug on the other side - both connections are UPC polished.

- Duplex cable with 50/125µm OM4 fibre type
- Cable material: sheath halogen-free and flame-retardant, violet
- LC connector: plug with high mechanical load capacity, push-pull latched with anti-rotation device, ceramic ferrule
- LSH connector: precisely manufactured connector with low return loss, ceramic ferrule
- UPC Polish (Ultra Physical Contact)
- IL < 0.25dB, RL > 25dB
- IL (typical) < 0.12dB
- Cable OD (outer diameter): 3.0 x 6.0mm

Technical specifications		
Manufacturer	ROLINE	
Product group	Fibre optic cable	
Product type	Fibre Optic Jumper Cables OM4	
Colour	violet	
Length	1 m	
Quantity of fibre	2	
Cable type	Duplex Cable	

External cable	Νο
Fibre section	50/125µm OM4
Connection ports	LSH / LC
Side 1 Connector Type	LSH
Side 2 Connector Type	LC
Kevlar strain relief	Yes
Cable LSOH	Yes