

# ROLINE FO Jumper Cable Duplex, 9/125µm, OS2, LSH/LC, APC Polish, LSOH, yellow, 1.0 m

<b>Product No.</b>	21.15.9481
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	21.15.9481
<b>EAN (single piece)</b>	7611990151875



**LSOH**

**High-quality fibre optic cable with the high protective, secured LSH connection on one side and LC plug on the other side - both connections are APC polished.**

- Duplex cable with fiber type 9/125µm OS2
- Cable material: sheath halogen-free and flame-retardant, yellow, solid core with aramid strain relief
- LC connector: connector with high mechanical load capacity, push-pull latched with anti-rotation lock, APC ground joint, ceramic ferrule
- LSH connector: precision-manufactured connectors with low return loss (RL), APC ground joint, ceramic ferrule, green
- The LSH connector has a spring-loaded shutter, which fully protects the ferrule from dust and scratches
- APC Polish (8° - APC - Angled Physical Contact - allows tighter connection and smaller end-face radii)
- IL < 0.25dB, RL > 60dB
- IL (typical) < 0.12dB
- Cable OD (outer diameter): 3.0 x 6.0mm

## Technical specifications

Manufacturer	ROLINE
Product group	Fibre optic cable
Product type	Fibre Optic Jumper Cables Singlemode
Colour	yellow
Length	1 m
Quantity of fibre	2
Cable type	Duplex Cable
External cable	No
Fibre section	9/125µm OS2
Connection ports	LSH / LC
Side 1 Connector Type	LSH
Side 2 Connector Type	LC
Kevlar strain relief	Yes
Cable LSOH	Yes