

Features

- Material: UL approved Nylon 66, 94V-2
- Color: Grey (RAL7001)
- Suit a variety of applications, and diverse industries.
- Function : Mount gland to pre-drilled panel hole, use locknut to fix gland on board, insert the cables in the seal, and then tighten up the nut to hold cables in position.
- Simply and quickly fixed, high degree of the protection IP68 preventing dust and water.

RS PRO Cable Gland

RS Stock No.: 2101375



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Material: UL approved Nylon 66, 94V-2*
- *Color: Grey(RAL7001), available in other colors.*
- *Suit a variety of applications, and diverse industries.*
- *Function :Mount gland to pre-drilled panel hole, use locknut to fix gland on board, insert the cables in the seal,and then tighten up the nut to hold cables in position.*
- *Feature : Simply and quickly fixed, high degree of the protection IP68 preventing dust and water.*
- *Available to order the accessories separately. Follow the drawing and add the letter to the suffix part number, L for locknut, W for washer, B for gland body, S for seal, N for nut.*

General Specifications

Series	PG Thread
Type	Cable Gland
Colour	Grey(RAL7001)
Material	Nylon 66
UV Resistant	No
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	85°C
Fire Behaviour	Self-Extinguishing
Quantity	25pcs

Mechanical Specifications

Thread	PG-9
Mounting Hole	15.2 + 0.2 mm
Cable Range	4 ~ 8 mm
Thread Length(L1)	8.2 mm

Protection Category

IP Rating	IP68
-----------	------

Approvals

Standards Met	UL, RoHS Certificate of compliance, CE
---------------	----------------------------------------

