## ROLINE S/FTP PiMF Cable Cat.7 (Class F), Solid Wire, 100m

Product No. Manufacturer Manufacturer No. EAN (single piece) 21.15.0001 ROLINE 21.15.0001 7611990173693





- Cable for structured building cabling
- Impedance: 100 Ohm
- 100 meter as coil
- 3P certified

• Construction: 8 lines, solid copper wire, AWG23 / Pairs shielded with aluminium foil / Complete shielding in copper braid

Technical specifications		
Manufacturer	ROLINE	
Product group	Twisted Pair Cable	
Product type	Installation cable	
Colour	grey	
Length	100 m	
Contents	100 m	
Shield type	SFTP	
Transfer quality	Cat7 / Class F	

Impedance	100 Ohm
Quantity of wires	8
Conductor cross section (AWG)	AWG 23
Conductor type	Solid wire
Cable LSOH	No
Material (external cable mantle)	PVC
Fire protection class	Eca
Weight	497.5 g
Height of packaging (single piece)	70 mm
Width of packaging (single piece)	370 mm
Depth of packaging (single piece)	370 mm
Package weight (single piece)	5.42 kg