## ROLINE S/FTP PiMF Cable Cat.7 (Class F), Solid Wire, LSOH, 100 m

Product No. Manufacturer Manufacturer No. EAN (single piece) 21.15.0002 ROLINE 21.15.0002 7611990199464







- Cable for structured building cabling
- Impedance: 100 Ohm
- 100 meter/box
- Construction:
- 8 lines, solid copper wire, AWG23
- pairs shielded with aluminium foil
- complete shielding in tinned copper braid
- Halogen-free, flame retardant, low smoke
- Colour: grey

Manufacturer

## Technical specifications ROLINE

Product group	Twisted Pair Cable	
Product type	Installation cable	
Colour	grey	
Length	100 m	
Contents	100 m	

Shield type	SFTP
Transfer quality	Cat7 / Class F
Impedance	100 Ohm
Quantity of wires	8
Conductor cross section (AWG)	AWG 23
Conductor type	Solid wire
Cable LSOH	Yes
Material (external cable mantle)	PVC
Fire protection class	Eca
Weight	4898.7 g
Height of packaging (single piece)	140 mm
Width of packaging (single piece)	310 mm
Depth of packaging (single piece)	310 mm
Package weight (single piece)	4.9 kg