## ROLINE S/FTP PiMF Cable Cat.7 (Class F), Solid Wire, 300m

Product No. Manufacturer Manufacturer No. EAN (single piece) 21.15.0003 ROLINE 21.15.0003 7611990173709







- Cable for structured building cabling
- Impedance: 100 Ohm
- 300 meter on wooden drum
- 3P certified

• Construction: 8 lines, solid copper wire, AWG23 / Pairs shielded with aluminium foil / Complete shielding in copper braid

Technical specifications		
Manufacturer	ROLINE	
Product group	Twisted Pair Cable	
Product type	Installation cable	
Colour	grey	
Length	300 m	
Contents	300 m	
Shield type	SFTP	
Transfer quality	Cat7 / Class F	

Impedance	100 Ohm
Quantity of wires	8
Conductor cross section (AWG)	AWG 23
Conductor type	Solid wire
Cable LSOH	No
Material (external cable mantle)	PVC
Fire protection class	Eca
Weight	17.11 kg
Height of packaging (single piece)	300 mm
Width of packaging (single piece)	450 mm
Depth of packaging (single piece)	450 mm
Package weight (single piece)	19.6 kg