

ROLINE S/FTP Cable Cat.6A (Class EA), Stranded, 300 m

Product No.	21.15.0882
Manufacturer	ROLINE
Manufacturer No.	21.15.0882
EAN (single piece)	7611990110377



Twisted pair network cable for assembly with RJ45 plugs

- Cable for structured building cabling
- 300 meter / box
- Impedance: 100 Ohm
- Construction:
 - 8 lines, solid copper wire, AWG23
 - pairs shielded with aluminium foil
 - complete shielding in tinned copper braid
- Colour: grey

For a structured Cat. 6a S/FTP Cabling we recommend to use the following components:

The following products combination has been tested by 3P Third Party Testing, Attestation of Cornformity No. 107549, in a Two Connector Channel of 100 meters:

- 21.15.0881 ROLINE S/FTP Cable, Cat. 6a, Solid Wire, AWG23
- 26.11.0366 ROLINE Cat. 6a Keystone, RJ-45, Shielded, Silver
- 21.15.0865 ROLINE S/FTP Patch Cable Cat. 6a, Grey

Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable
Product type	Raw cable Cat.6A
Colour	grey
Length	300 m
Contents	300 m
Shield type	SFTP
Transfer quality	Cat6A / Class EA
Impedance	100 Ohm
Quantity of wires	8
Conductor type	Wire
Cable LSOH	No
Material (external cable mantle)	PVC
Weight	11.11 kg
Height of packaging (single piece)	380 mm
Width of packaging (single piece)	360 mm
Depth of packaging (single piece)	350 mm
Package weight (single piece)	13.4 kg