ROLINE S/FTP Cable Cat.6A (Class EA), LSOH, Solid Wire, 300 m

Product No. 21.15.0884

ROLINE

Manufacturer No. 21.15.0884

EAN (single piece) 7611990148318





Manufacturer



Cable for structured building cabling

• 300 meter / box

• Impedance: 100 Ohm

• Construction:

- 8 lines, solid copper wire, AWG23

- pairs shielded with aluminium foil

- complete shielding in tinned copper braid

Colour: grey

For a structured Cat. 6a S/FTP Cabling we recommend to use the following components:

21.15.0884 ROLINE S/FTP Cable, Cat. 6a, Solid Wire, AWG23

25.16.8579 Flush Mount Wall Oulet for Keystones, 2-port

26.11.0367 ROLINE Cat. 6a Keystone, RJ-45, Shielded, Silver

26.11.0359/.0360 ROLINE Patchpanel for Keystones 19", 24x

21.15.2705 ROLINE S/FTP Patch Cable Cat. 6a, Grey

Technical specifications		
Manufacturer	ROLINE	
Product group	Twisted Pair Cable	

Product type	Installation cable
Colour	grey
Length	300 m
Contents	300 m
Shield type	SFTP
Transfer quality	Cat6A / Class EA
Impedance	100 Ohm
Quantity of wires	8
Conductor type	Solid wire
Cable LSOH	Yes
Material (external cable mantle)	LSOH
Fire protection class	Eca
Weight	20 kg
Height of packaging (single piece)	200 mm
Width of packaging (single piece)	300 mm
Depth of packaging (single piece)	300 mm
Package weight (single piece)	20 kg