ROLINE S/FTP Patch Cord Cat.6A, Component Level, LSOH, yellow, 10 m

Product No. 21.15.2827


Manufacturer ROLINE

Manufacturer No. 21.15.2827

EAN (single piece) 7611990155248















- Patch cable for networking connections between devices.
- Prepared double shielded Twisted Pair cable with screened RJ-45 connectors on both ends.
- Durable due to moulded kink protection.
- Flexible cable, suitable for narrow bending.
- High quality plugs with gold plated contacts.
- Contact settings 1:1, in accordance with the EIA/TIA 568 standard.
- Construction: 4-pair stranded copper wire.
- Complete braid shielding. Pairs shielded with aluminium clad polyester foil.

100% Component Level testing

| Technical specifications | | |
|--------------------------|--------------------|--|
| Manufacturer | ROLINE | |
| Product group | Twisted Pair Cable | |
| Product type | S/FTP Patchcord | |
| Colour | yellow | |
| Length | 10 m | |

| Shield type | SFTP |
|------------------------------------|------------------|
| Transfer quality | Cat6A / Class EA |
| Component-Level certified | Yes |
| Quantity of wires | 8 |
| Conductor type | Wire |
| Crossed | No |
| Colour (Spout) | yellow |
| Cable LSOH | Yes |
| Side 1 Connector Type | RJ-45 |
| Side 1 Connector Gender | Male |
| Side 2 Connector Type | RJ-45 |
| Side 2 Connector Gender | Male |
| Connector Type RJ45 | Standard |
| Weight | 359 g |
| Height of packaging (single piece) | 50 mm |
| Width of packaging (single piece) | 190 mm |
| Depth of packaging (single piece) | 170 mm |
| Package weight (single | 0.371 kg |

piece)