

# ROLINE S/FTP Patch Cord Cat.6A, Component Level, LSOH, yellow, 20 m

**Product No.** 21.15.2829  
**Manufacturer** ROLINE  
**Manufacturer No.** 21.15.2829  
**EAN (single piece)** 7611990155279

**roline**  
Designed for Professionals



- Patch cable for networking connections between devices.
- Prepared double shielded Twisted Pair cable with screened RJ-45 connectors on both ends.
- Durable due to moulded kink protection.
- Flexible cable, suitable for narrow bending.
- High quality plugs with gold plated contacts.
- Contact settings 1:1, in accordance with the EIA/TIA 568 standard.
- Construction: 4-pair stranded copper wire.
- Complete braid shielding. Pairs shielded with aluminium clad polyester foil.

## 100% Component Level testing

### Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable
Product type	S/FTP Patchcord
Colour	yellow
Length	20 m

Shield type	SFTP
Transfer quality	Cat6A / Class EA
Component-Level certified	Yes
Quantity of wires	8
Conductor type	Wire
Crossed	No
Colour (Spout)	yellow
Cable LSOH	Yes
Side 1 Connector Type	RJ-45
Side 1 Connector Gender	Male
Side 2 Connector Type	RJ-45
Side 2 Connector Gender	Male
Connector Type RJ45	Standard
Weight	741.4 g
Height of packaging (single piece)	80 mm
Width of packaging (single piece)	200 mm
Depth of packaging (single piece)	200 mm
Package weight (single piece)	0.723 kg