

ROLINE S/FTP Patch Cord Cat.6A, Component Level, LSOH, white, 7.5 m

| | |
|---------------------------|---------------|
| Product No. | 21.15.2866 |
| Manufacturer | ROLINE |
| Manufacturer No. | 21.15.2866 |
| EAN (single piece) | 7611990159574 |



- Patch cable for networking connections between devices.
- Prepared double shielded Twisted Pair cable with screened RJ-45 connectors on both ends.
- Durable due to moulded kink protection.
- Flexible cable, suitable for narrow bending.
- High quality plugs with gold plated contacts.
- Contact settings 1:1, in accordance with the EIA/TIA 568 standard.
- Construction: 4-pair stranded copper wire.
- Complete braid shielding. Pairs shielded with aluminium clad polyester foil.

100% Component Level testing

Technical specifications

| | |
|---------------|--------------------|
| Manufacturer | ROLINE |
| Product group | Twisted Pair Cable |
| Product type | S/FTP Patchcord |
| Colour | white |
| Length | 7.5 m |

| | |
|------------------------------------|------------------|
| Shield type | SFTP |
| Transfer quality | Cat6A / Class EA |
| Component-Level certified | Yes |
| Quantity of wires | 8 |
| Conductor type | Wire |
| Crossed | No |
| Colour (Spout) | red |
| Cable LSOH | Yes |
| Side 1 Connector Type | RJ-45 |
| Side 1 Connector Gender | Male |
| Side 2 Connector Type | RJ-45 |
| Side 2 Connector Gender | Male |
| Connector Type RJ45 | Standard |
| Weight | 266.9 g |
| Height of packaging (single piece) | 40 mm |
| Width of packaging (single piece) | 180 mm |
| Depth of packaging (single piece) | 190 mm |
| Package weight (single piece) | 0.283 kg |