

ROLINE S/FTP Patch Cord Cat.6A, Component Level, LSOH, white, 0.3 m

Product No.	21.15.2976
Manufacturer	ROLINE
Manufacturer No.	21.15.2976
EAN (single piece)	7611990159505



- Patch cable for networking connections between devices.
- Prepared double shielded Twisted Pair cable with screened RJ-45 connectors on both ends.
- Durable due to moulded kink protection.
- Flexible cable, suitable for narrow bending.
- High quality plugs with gold plated contacts.
- Contact settings 1:1, in accordance with the EIA/TIA 568 standard.
- Construction: 4-pair stranded copper wire.
- Complete braid shielding. Pairs shielded with aluminium clad polyester foil.

100% Component Level testing

Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable
Product type	S/FTP Patchcord
Colour	white
Length	0.3 m

Shield type	SFTP
Transfer quality	Cat6A / Class EA
Component-Level certified	Yes
Quantity of wires	8
Conductor type	Wire
Crossed	No
Colour (Spout)	red
Cable LSOH	Yes
Side 1 Connector Type	RJ-45
Side 1 Connector Gender	Male
Side 2 Connector Type	RJ-45
Side 2 Connector Gender	Male
Connector Type RJ45	Standard
Weight	20.3 g
Height of packaging (single piece)	10 mm
Width of packaging (single piece)	100 mm
Depth of packaging (single piece)	120 mm
Package weight (single piece)	0.033 kg