

## FEATURES

- A very reliable plug, rated at 10 Amps, with a screw connection for the lead wire and a screw-on rigid acetal moulding. Accepts up to 7,1mm diameter cable with a conductor of 3,5mm diameter

# RS PRO Banana Plugs & Connectors-4mm Banana Plug Blue

RS Stock No.: 2121239



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

A very reliable plug rated at 10 Amps with a screw connection for the lead wire and a screw-on rigid acetal moulding. Accepts up to 7,1mm diameter cable with a conductor of 3,5mm diameter

## General Specifications

Type	Triple Contact Plug
Colour	Blue
Gender	Male
Contact Material	Brass
Contact Plating	Nickel

## Electrical Specifications

Voltage Rating	50V
Current Rating	10A
Connector Size	2mm
Termination Method	Screw
Insulation Material	Polyoxymethylene

## Mechanical Specifications

Length	49.8mm
--------	--------

## Approvals

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

## Similar Products

Parameters	Stock# 423-201	Stock# 423-239	Stock# 103-7637	Stock# 454-283
Brand	RS PRO	RS PRO	RS PRO	RS PRO
Colour	Black	Red	Red	Black
Gender	Female	Female	Male	Male
Contact Material	Brass	Brass	Stainless Steel	Brass
Voltage Rating	50V dc	50V dc	50V	1kV
Current Rating	16A	16A	30A	30A
Termination Method	Solder	Solder	Solder	Solder
Insulation Material	POM	POM		PP
Length	52.9mm	52.9mm		
Height Above Panel	24mm to 32mm	24mm to 32mm	24mm to 32mm	

Overall Diameter	14mm	14mm	14mm	
Thread Size	4BA clearance	4BA clearance		
Maximum Panel Thickness	12.7mm			

## Product Dimensions Details

### Dimensions

MAXIMUM CONDUCTOR SIZE 3.5mm

